



Genomic tracks for chromosome 10p11.21, showing a gene model, a heatmap of 1000 Genomes Project samples, and a heatmap of 1000 Genomes Project samples. The gene model shows the structure of the gene, including exons and introns. The heatmaps show the frequency of alleles across the population.

Gene model: **SLC6A14** (SLC6A14-AS1, SLC6A14-AS2, SLC6A14-AS3, SLC6A14-AS4, SLC6A14-AS5, SLC6A14-AS6, SLC6A14-AS7, SLC6A14-AS8, SLC6A14-AS9, SLC6A14-AS10, SLC6A14-AS11, SLC6A14-AS12, SLC6A14-AS13, SLC6A14-AS14, SLC6A14-AS15, SLC6A14-AS16, SLC6A14-AS17, SLC6A14-AS18, SLC6A14-AS19, SLC6A14-AS20, SLC6A14-AS21, SLC6A14-AS22, SLC6A14-AS23, SLC6A14-AS24, SLC6A14-AS25, SLC6A14-AS26, SLC6A14-AS27, SLC6A14-AS28, SLC6A14-AS29, SLC6A14-AS30, SLC6A14-AS31, SLC6A14-AS32, SLC6A14-AS33, SLC6A14-AS34, SLC6A14-AS35, SLC6A14-AS36, SLC6A14-AS37, SLC6A14-AS38, SLC6A14-AS39, SLC6A14-AS40, SLC6A14-AS41, SLC6A14-AS42, SLC6A14-AS43, SLC6A14-AS44, SLC6A14-AS45, SLC6A14-AS46, SLC6A14-AS47, SLC6A14-AS48, SLC6A14-AS49, SLC6A14-AS50, SLC6A14-AS51, SLC6A14-AS52, SLC6A14-AS53, SLC6A14-AS54, SLC6A14-AS55, SLC6A14-AS56, SLC6A14-AS57, SLC6A14-AS58, SLC6A14-AS59, SLC6A14-AS60, SLC6A14-AS61, SLC6A14-AS62, SLC6A14-AS63, SLC6A14-AS64, SLC6A14-AS65, SLC6A14-AS66, SLC6A14-AS67, SLC6A14-AS68, SLC6A14-AS69, SLC6A14-AS70, SLC6A14-AS71, SLC6A14-AS72, SLC6A14-AS73, SLC6A14-AS74, SLC6A14-AS75, SLC6A14-AS76, SLC6A14-AS77, SLC6A14-AS78, SLC6A14-AS79, SLC6A14-AS80, SLC6A14-AS81, SLC6A14-AS82, SLC6A14-AS83, SLC6A14-AS84, SLC6A14-AS85, SLC6A14-AS86, SLC6A14-AS87, SLC6A14-AS88, SLC6A14-AS89, SLC6A14-AS90, SLC6A14-AS91, SLC6A14-AS92, SLC6A14-AS93, SLC6A14-AS94, SLC6A14-AS95, SLC6A14-AS96, SLC6A14-AS97, SLC6A14-AS98, SLC6A14-AS99, SLC6A14-AS100, SLC6A14-AS101, SLC6A14-AS102, SLC6A14-AS103, SLC6A14-AS104, SLC6A14-AS105, SLC6A14-AS106, SLC6A14-AS107, SLC6A14-AS108, SLC6A14-AS109, SLC6A14-AS110, SLC6A14-AS111, SLC6A14-AS112, SLC6A14-AS113, SLC6A14-AS114, SLC6A14-AS115, SLC6A14-AS116, SLC6A14-AS117, SLC6A14-AS118, SLC6A14-AS119, SLC6A14-AS120, SLC6A14-AS121, SLC6A14-AS122, SLC6A14-AS123, SLC6A14-AS124, SLC6A14-AS125, SLC6A14-AS126, SLC6A14-AS127, SLC6A14-AS128, SLC6A14-AS129, SLC6A14-AS130, SLC6A14-AS131, SLC6A14-AS132, SLC6A14-AS133, SLC6A14-AS134, SLC6A14-AS135, SLC6A14-AS136, SLC6A14-AS137, SLC6A14-AS138, SLC6A14-AS139, SLC6A14-AS140, SLC6A14-AS141, SLC6A14-AS142, SLC6A14-AS143, SLC6A14-AS144, SLC6A14-AS145, SLC6A14-AS146, SLC6A14-AS147, SLC6A14-AS148, SLC6A14-AS149, SLC6A14-AS150, SLC6A14-AS151, SLC6A14-AS152, SLC6A14-AS153, SLC6A14-AS154, SLC6A14-AS155, SLC6A14-AS156, SLC6A14-AS157, SLC6A14-AS158, SLC6A14-AS159, SLC6A14-AS160, SLC6A14-AS161, SLC6A14-AS162, SLC6A14-AS163, SLC6A14-AS164, SLC6A14-AS165, SLC6A14-AS166, SLC6A14-AS167, SLC6A14-AS168, SLC6A14-AS169, SLC6A14-AS170, SLC6A14-AS171, SLC6A14-AS172, SLC6A14-AS173, SLC6A14-AS174, SLC6A14-AS175, SLC6A14-AS176, SLC6A14-AS177, SLC6A14-AS178, SLC6A14-AS179, SLC6A14-AS180, SLC6A14-AS181, SLC6A14-AS182, SLC6A14-AS183, SLC6A14-AS184, SLC6A14-AS185, SLC6A14-AS186, SLC6A14-AS187, SLC6A14-AS188, SLC6A14-AS189, SLC6A14-AS190, SLC6A14-AS191, SLC6A14-AS192, SLC6A14-AS193, SLC6A14-AS194, SLC6A14-AS195, SLC6A14-AS196, SLC6A14-AS197, SLC6A14-AS198, SLC6A14-AS199, SLC6A14-AS200, SLC6A14-AS201, SLC6A14-AS202, SLC6A14-AS203, SLC6A14-AS204, SLC6A14-AS205, SLC6A14-AS206, SLC6A14-AS207, SLC6A14-AS208, SLC6A14-AS209, SLC6A14-AS210, SLC6A14-AS211, SLC6A14-AS212, SLC6A14-AS213, SLC6A14-AS214, SLC6A14-AS215, SLC6A14-AS216, SLC6A14-AS217, SLC6A14-AS218, SLC6A14-AS219, SLC6A14-AS220, SLC6A14-AS221, SLC6A14-AS222, SLC6A14-AS223, SLC6A14-AS224, SLC6A14-AS225, SLC6A14-AS226, SLC6A14-AS227, SLC6A14-AS228, SLC6A14-AS229, SLC6A14-AS230, SLC6A14-AS231, SLC6A14-AS232, SLC6A14-AS233, SLC6A14-AS234, SLC6A14-AS235, SLC6A14-AS236, SLC6A14-AS237, SLC6A14-AS238, SLC6A14-AS239, SLC6A14-AS240, SLC6A14-AS241, SLC6A14-AS242, SLC6A14-AS243, SLC6A14-AS244, SLC6A14-AS245, SLC6A14-AS246, SLC6A14-AS247, SLC6A14-AS248, SLC6A14-AS249, SLC6A14-AS250, SLC6A14-AS251, SLC6A14-AS252, SLC6A14-AS253, SLC6A14-AS254, SLC6A14-AS255, SLC6A14-AS256, SLC6A14-AS257, SLC6A14-AS258, SLC6A14-AS259, SLC6A14-AS260, SLC6A14-AS261, SLC6A14-AS262, SLC6A14-AS263, SLC6A14-AS264, SLC6A14-AS265, SLC6A14-AS266, SLC6A14-AS267, SLC6A14-AS268, SLC6A14-AS269, SLC6A14-AS270, SLC6A14-AS271, SLC6A14-AS272, SLC6A14-AS273, SLC6A14-AS274, SLC6A14-AS275, SLC6A14-AS276, SLC6A14-AS277, SLC6A14-AS278, SLC6A14-AS279, SLC6A14-AS280, SLC6A14-AS281, SLC6A14-AS282, SLC6A14-AS283, SLC6A14-AS284, SLC6A14-AS285, SLC6A14-AS286, SLC6A14-AS287, SLC6A14-AS288, SLC6A14-AS289, SLC6A14-AS290, SLC6A14-AS291, SLC6A14-AS292, SLC6A14-AS293, SLC6A14-AS294, SLC6A14-AS295, SLC6A14-AS296, SLC6A14-AS297, SLC6A14-AS298, SLC6A14-AS299, SLC6A14-AS300, SLC6A14-AS301, SLC6A14-AS302, SLC6A14-AS303, SLC6A14-AS304, SLC6A14-AS305, SLC6A14-AS306, SLC6A14-AS307, SLC6A14-AS308, SLC6A14-AS309, SLC6A14-AS310, SLC6A14-AS311, SLC6A14-AS312, SLC6A14-AS313, SLC6A14-AS314, SLC6A14-AS315, SLC6A14-AS316, SLC6A14-AS317, SLC6A14-AS318, SLC6A14-AS319, SLC6A14-AS320, SLC6A14-AS321, SLC6A14-AS322, SLC6A14-AS323, SLC6A14-AS324, SLC6A14-AS325, SLC6A14-AS326, SLC6A14-AS327, SLC6A14-AS328, SLC6A14-AS329, SLC6A14-AS330, SLC6A14-AS331, SLC6A14-AS332, SLC6A14-AS333, SLC